



Simonswerk Door Preparation

Universal Milling Frame
Jig for Routing Templates

Special Order

Precise routings can be conducted for a certain hinge using the corresponding routing template.



Stock # 5 250930 0 000 Net \$ 316

Complete jig consists of:

- 1 universal frame
- 1 clamping device

Fitting instructions:

1. Secure the clamping device to the routing frame using the clamp rods.
2. Roughly adjust the clamping device according to rebate construction and fix in place with fastening screws.
3. Clamp routing frame to workpiece with clamping wheel.
4. Insert template and roughly adjust using the standard values given for rail and angle.
5. Carry out fine adjustment using spindles.

Recommended bit & collet:

- 45441: Plunge bit 3/4" x 2"
- 42030: 1" collet

Routing Templates

In Stock:
See page 820
MP Catalog



For	Description	List/ea
For 240 Hinge		
RT-DOOR-240	Routing Template, Door	\$ 75.22
RT-FRAME-240	Routing Template, Frame	75.22
For 340 Hinge		
RT-DOOR-340	Routing Template, Door	\$ 62.68
RT-FRAME-340	Routing Template, Frame	62.68
For 540 Hinge		
RT-540-S1	For TE-540-3D, Step 1	\$ 62.68
RT-540-S2	For TE-540-3D, Step 2	62.68
RT-540-A8-S3	For TE-540-3D-A8, Step 3	62.68
For 640 Hinge		
RT-640-S1	For TE-640-3D, Step 1	\$ 62.68
RT-640-S2	For TE-640-3D, Step 2	62.68

Visit www.tectushinges.com/adjust_steps.html for an active look at Tectus 3D adjustments - step by step

TECTUS® 3D ADJUSTMENT Vertical Adjustment : Step 1

- Vertical Adjustment : Step 1**
Slightly loosen the clamping screws using the 4mm hex key.
- Vertical Adjustment : Step 2**
Adjust the vertical position of the door by turning the lower height adjustment screw. Turn the upper height adjustment screw in the opposite direction if necessary.
Retighten the clamping screws
- Slide-to-Side Adjustment**
Adjust the spindles using a 4mm Allen key
Towards hinge : twist left (max. 3mm)
Towards lock : twist right (max. 3mm)
- Depth Adjustment**
Slightly loosen the fixing screws.
Put the door at the correct depth.
Retighten the clamping screws.

for specification, pricing, and installation support contact a TECTUS® dealer

YouTube

See Video at macmurraypacific.com/videos.html#simonswerk for installation of Tectus hinges using Universal Milling Frame and Templates.



Sales Bulletin
Sept 2016

**Update
March 2018
New Mounts**

**Simonswerk Tectus
Display Mounts**

Large Simonswerk Tectus
Display Mount

Available in 2 Widths:
16" and 24".

Both Sizes show the same
amount of product.

Display free of charge.

Drop Ship,
\$ 200 freight charge.



24" width

**Simonswerk Tectus
Hinge Mounts**



MOUNT-340-F1
Satin Chrome Look
\$ 60



MOUNT-340-F2
Satin Nickel Look
\$ 60

**Adapts Tectus hinge to Std thickness
Pre-hung door frames**



MOUNT-340-PLATE - Tectus 340 hinge with fixing plate



MOUNT-340-UMBER
Rustic Umber Finish
\$ 60